



aktiv8T

SKU: S2068T

Sachtler aktiv8T fluid head Touch & Go with SpeedLevel and SpeedSwap technology



PRODUCT DESCRIPTION

This Sachtler aktiv™ 75 mm fluid head for payloads of up to 12 kg (26.5 lbs.), with unique SpeedLevel™ technology, can be levelled in seconds giving you time to get the perfect shot in documentary, corporate or news applications. The SpeedSwap™ system delivers the fastest way to switch between tripod and slider in seconds giving you ultimate flexibility.

Product Highlights

- Level and lock your head in an instant without missing a second of action
Unique SpeedLevel technology.
- Visible from any height or angle - day or night.
Innovative PrismBubble.
- Capture extreme low angle shots right down to the ground.
Innovative streamlined mounting system.
- Switch between tripod and slider in seconds.
Revolutionary SpeedSwap system.
- Create moving stories, whatever the weather.
Performance tested to the extreme.

TECHNICAL SPECIFICATIONS




Range	aktiv
Temperature Range	-40 °C to 60 °C -40 °F to 140 °F
Camera Plate	Touch & Go plate S
Payload	0 kg to 12 kg 0 lb to 26.46 lb
Counterbalance	15 + 0 steps
Drag	7 + 0 drag settings
Weight	2.8 kg 6.17 lb
Bowl Size	75 mm
Pan Bar Count	1
Sliding Range	60 mm 2.36 in
Tilt Range	90° to -70°
Pan Bar Length	43 cm to 16.93 in to
Pan Bar Type	Pan bar DV 75
Pan Bar Attachment	16/-/28 mm
Level Bubble	Yes, illuminated
Battery Type	CR2032

IN THE BOX

- aktiv8T fluid head with one pan bar DV 75 and one Touch & Go plate S
- flowtech75 metal bowl insert (to upgrade flowtech75 tripods for optimum performance with aktiv fluid heads) and Service Centre flowtech upgrade instructions.
- [Touch & Go plate S](#) (0364)
- [aktiv bowl connector 75mm V2](#) (S2080-0012)
- [flowtech75 metal bowl insert](#) (S2051-1066)
- [Pan bar DV 75](#) (0992SP)

DIAGRAMS

Payload Diagram aktiv8, aktiv8T and aktiv10



YOU MAY ALSO LIKE...



[System aktiv8T
flowtech75 MS](#)



[System aktiv8T
flowtech75 GS](#)



[System aktiv8
flowtech75 MS](#)



[aktiv bowl connector
75mm V2](#)